# **FloBoss<sup>™</sup> S600+ Flow Computer**

The FloBoss<sup>™</sup> S600+ Flow Computer (S600+) is a panelmount fiscal flow computer designed specifically for hydrocarbon liquid and gas measurement where versatility and accuracy are high priorities. The FloBoss S600+ builds on the success of its predecessor, the S600, which has been the market-leading panel-mount flow computer from Emerson Process Management.

The standard features of the S600+ make it ideal for the following applications:

- Fiscal flow measurement
- Custody transfer
- Pipeline measurement
- Batch loading
- Meter proving applications
- Single or multi-stream measurement
- Flow control

The S600+ supports multi-stream (up to ten with optional expansion modules), multi-station (up to two) applications that are configured for simultaneous metering of gas, wet gas, crude oil, refined products, LPG, NGLs, etc. The S600+ can accommodate both a liquid and a gas station simultaneously.

Supported flow meters or primary elements include turbine, ultrasonic, Coriolis, positive displacement, orifice, Venturi, Annubar, V-Cone<sup>®</sup>, and Rosemount conditioning orifice plate.

The S600+ supports an unprecedented number of global measurement standards including those covered by AGA, ISO, GPA, and GERG for gas applications, and API, ASTM, GPA, and NORSOK for liquid applications.

The S600+ uses distributed processing to achieve maximum performance. The S600+ contains a more powerful main processor than the original S600. The new CPU incorporates a hardware floating point processor and performs faster calculations than before, minimizing uncertainty and maximizing control.

Each additional expansion module utilizes local processors. The local processors convert inputs from field instrumentation into engineering units and drive output signals for process control. Background checks are performed continuously and locally in each module to assure operational validity.

All metering calculations are performed using 64-bit (double) precision floating point numbers for the highest accuracy and API compliance. Cumulative totals are stored in three separate memory locations (Tri-reg format) for maximum integrity. The LogiCalc user language allows double precision mathematical functions to be performed on database objects.

Data logging and archiving capabilities have been significantly increased, and include an extended historian. A typical archive for a ten-stream application would include 333 days of monthly, weekly, daily and hourly reports; plus 50,000 events and 50,000 alarms. Support for FLOWCAL CFX files has been added for enhanced data integrity.

The S600+ includes an eight-line LCD display and a 29-key keypad. The display and keypad on the S600+ enable you to review or modify system parameters without the need for a PC. The display supports both English and Russian character sets.

# Compatibility

The S600+ is fully backwards-compatible with the previous S600 model. The device utilizes existing configurations and tools that you are familiar with. This saves you time otherwise spent on learning and configuring with new tools, and helps to preserve your previous capital investments. You can easily convert existing S600 units to S600+ units, bringing all the benefits of the new product to your existing installation.



FloBoss S600+ Flow Computer



The S600+ has been designed to safeguard the future supply and support of the S600 family for many years to come. Investing in the new S600+ is low risk because the metrological calculations and code utilized in the S600+ has already been field proven in the S600. The S600+ provides increased processing power and memory. This allows Remote Automation Solutions to continue to add new features and functionality to the S600+, and ensures that users continue to benefit from their investment.

## Communications

The S600+ offers multiple communication options that allow you to interface to a variety of devices (including intelligent primary elements such as USM and Coriolis meters, for which the S600+ has many embedded drivers). The S600+ can be connected to serial and network printers. The increased communication capability of the S600+ enables you to maximize the benefits that are being increasingly realized with these intelligent meters.

Additionally, you can use the same communication ports to access the process data that is calculated and stored by the S600+. Available communication interfaces include the following:

- Two independent Ethernet 10/100baseT ports.
- HART<sup>®</sup> communication is facilitated using an optional 12-channel HART module, supporting point-to-point and multi-drop architectures (up to 50 transmitters).
- An embedded web server allows remote access to the flow computer. This allows for remote diagnostics, report access, and configuration. Security is provided by way of user name and password protection with a detailed event log for audit purposes. Compatible with Windows<sup>®</sup> Internet Explorer<sup>®</sup> version 5 or greater (version 9 or greater must use compatibility mode).
- Two configurable EIA-232 (RS-232) serial ports for connection to a printer or RTU.
- Seven EIA-422/485 (RS-422/RS-485) serial ports (up to 57600 bps baud) for connection to intelligent meters, Modbus SCADA data networks, or a DCS Supervisory System.
- USB 2.0 port for downloading reports and alarm/event logs.
- One dedicated configuration port for connection to the Config600<sup>™</sup> configuration software.

# Inputs/Outputs

The S600+ is supplied with one I/O (P144) module with one Pulse Mezzanine (P148) module. This provides multiple digital, analog, and pulse inputs and outputs. You can add two additional expansion modules to the S600+. The following expansion modules are available:

- I/O (P144) module Provides additional analog and digital I/O.
- Prover (P154) module Provides I/O for applications with a prover.
- HART (P188) module Provides I/O for applications with HART transmitters.
- Pulse Mezzanine (P148) module Provides pulse input capability.
  - **Note:** The Pulse Mezzanine module is installed as a daughterboard on an P144 or P154 module, and does not use an additional module slot.

# Configuration

Configuration of the S600+ is done through the same Windows-based intelligent set-up tool as the S600 (Config600 Lite, Config600 Lite+, or Config600 Pro). You can create or edit configuration files using Config600 Lite+ and Config600 Pro (refer to Specification Sheet Config600). The S600+ provides the following functions through the Config600 configuration tool:

- Stream and station totalization.
- Batch totalization and retro-calculation.
- 3-term PID control with optional secondary control.
- Flow balancing.
- Flow scheduling.
- Automatic proving sequence, including control of two provers by a single S600+.
- Support for Modbus/TCP or Modbus over Ethernet (10/100 Mbit/s full duplex).
- Sampler control.
- Station densitometer.
- Station gas chromatograph.
- Comprehensive maintenance mode.
- Coriolis meter interface.
- Ultrasonic meter interface.

The S600+ can store up to 20 different user configurations which minimizes downtime in the event a replacement is required.

FloBoss S600+ I	low Computer
-----------------	--------------

CPU Module			
Processor	ColdFire® MPC8313 333 MHz with integral floating point processor		
Operating System	Linux		
Memory	Flash	256 MB	
	DRAM	128 MB	
	SRAM	4 MB	
	(battery backed)	Battery Type	Lithium, 3 V, 1500 mAh (CR12600SE)
		Battery Life (typical)	5 to 7 years
		Hold-up Time (without power)	18 months
		Battery Backup Hold Time (after battery has failed its load test)	3 months at 20 °C
Data Logging	<ul> <li>The S600+ supports up to 333 days of reports from a 10 stream application, where monthly, weekly, daily, and hourly reports are each archived as standard individual reports.</li> <li>Example: 11 months of monthly, weekly, daily, and hourly reports; plus 50,000 events and 50,000 alarms.</li> <li>Note: Should additional data archiving be required, the individual hourly reports can be stored within their respective daily reports.</li> </ul>		
FlowCal CFX files	Common exchange f Liquid Ultrasonic, Liq 12)	ile format (CFX) files o uid Coriolis, or Liquid	direct from S600+ via webserver for Gas Ultrasonic, Turbines (gas records type 2, liquid records type
Form C Watchdog Relay	Contact Form	Change-over conta	cts
	Max Current	1 A	
	Max Voltage	50 Vdc	
	Maximum Power	30 VA	
	Control	Released on de-pov	wer, watchdog restart, or software-controlled
Clock	Туре	Battery-backed cal	endar clock
	Clock Accuracy	0.5 seconds per day	У
Calculations			
Gas	AGA 3 (Volume and Mass), AGA 5, AGA 7, AGA 8, AGA 10 Supports AGA9, using AGA7 to correct to base conditions Supports AGA11, using AGA8 to correct to base conditions ISO 5167, ISO 6976, ISO12213 – 2 & 3 API 21.1 GPA 2172 & 2145 NX 19, NX 19 Mod S-GERG, M-GERG VDI/VDE 2040 PTZ Annubar V-Cone		

Liquid			
•	API CH 11.1 – 2004 /	ASTM D 1250-04 / IP 200/04 and Addendum 1 2007	
	ASTM D 1250-1980 and API MPMS Chapter 11.1 – 1980 (Tables 5, 5A, 5B, 5D, 6, 6A, 6B, 6C,		
	6D, 23, 23A, 23B, 23I	D, 23E, 24, 24A, 24B, 24C, 24D, 24E, 53, 53A, 53B, 54, 54A, 54B, 54C, 50B)	
	ASTM/API 1952 (lookup tables for table 5, 6, 23 and 24) ASTM/API 1952 (algorithm support for tables 23, 24, 53, and 54)		
	API 11.1, API 11.2.1, API 11.2	API 11.2.1M, API 11.2.2, API 11.2.2M, API 11.2.4	
	API 12.2.1, API 12.2.2	2, API 12.2.3, API 2540	
	API 21.2		
	ASTM D1555 & D155	5M	
	GPA TP15, GPA TP16	, GPA TP25, GPA TP27	
	Propylene API 11.3.2	2	
	Ethylene IUPAC, NIST	1045 & API 11.3.2.1	
	ISU 91/1 (IP2), ISU 91	/2 (IP3)	
	NORSOK I-105 Appex	D (water in oil)	
	Downer 1979 calcula	tion of CPI	
	ISO 17089-1 Annex E	(Daniel ultrasonic meters, correction of meter geometry)	
	NPD		
	Densitometer algorit	hms Solartron/Micro Motion, Sarasota/PEEK	
Prover	Compact, uni-directional, bi-directional, master meter, dual chronometry		
	Support for NORSOK	statistical evaluation of repeatability	
	Support for 1, 2, or 4	sphere switches	
	Each S600+ can supp	ort up to two provers (not simultaneously)	
	Note: Master meter (	MM) proving support for MM volume vs Stream volume, MM mass vs and MM volume vs Stream mass	
Communications	5000000		
Configuration Port (located on	Connector	6-nin R112	
Configuration Port (located on the bottom of the front panel)	Connector	0-pinkj12	
the bottom of the front panel)	Communication	חבבבאם	
the bottom of the front panel)	Communication Standard	RS232D	
the bottom of the front panel)	Communication Standard Signals Supplied	RS232D Tx, Rx, CTS, GND	
the bottom of the front panel)	Communication Standard Signals Supplied Baud Rate	RS232D Tx, Rx, CTS, GND 2400, 4800, 9600, 19200, 38400, 57600	
the bottom of the front panel)	Communication Standard Signals Supplied Baud Rate Format	RS232D Tx, Rx, CTS, GND 2400, 4800, 9600, 19200, 38400, 57600 Config600 Protocol	
the bottom of the front panel) Ethernet	Communication Standard Signals Supplied Baud Rate Format Speed	RS232D Tx, Rx, CTS, GND 2400, 4800, 9600, 19200, 38400, 57600 Config600 Protocol 10 or 100 Mb/s, full Duplex	
the bottom of the front panel) Ethernet (NTWK1, NTWK2)	Communication Standard Signals Supplied Baud Rate Format Speed Media Connectivity	RS232D Tx, Rx, CTS, GND 2400, 4800, 9600, 19200, 38400, 57600 Config600 Protocol 10 or 100 Mb/s, full Duplex 10 or 100baseT, twisted pair utilizing standard RJ45	
the bottom of the front panel) Ethernet (NTWK1, NTWK2)	Communication Standard Signals Supplied Baud Rate Format Speed Media Connectivity Protocol	RS232D Tx, Rx, CTS, GND 2400, 4800, 9600, 19200, 38400, 57600 Config600 Protocol 10 or 100 Mb/s, full Duplex 10 or 100baseT, twisted pair utilizing standard RJ45 Modbus/TCP or Modbus over Ethernet	
the bottom of the front panel) Ethernet (NTWK1, NTWK2)	Communication Standard Signals Supplied Baud Rate Format Speed Media Connectivity Protocol	RS232D Tx, Rx, CTS, GND 2400, 4800, 9600, 19200, 38400, 57600 Config600 Protocol 10 or 100 Mb/s, full Duplex 10 or 100baseT, twisted pair utilizing standard RJ45 Modbus/TCP or Modbus over Ethernet Master, slave, and peer-to-peer	
the bottom of the front panel) Ethernet (NTWK1, NTWK2)	Communication Standard Signals Supplied Baud Rate Format Speed Media Connectivity Protocol	RS232D Tx, Rx, CTS, GND 2400, 4800, 9600, 19200, 38400, 57600 Config600 Protocol 10 or 100 Mb/s, full Duplex 10 or 100baseT, twisted pair utilizing standard RJ45 Modbus/TCP or Modbus over Ethernet Master, slave, and peer-to-peer Support for gas chromatographs, ultrasonic (Daniel, Instromet, Coldea, and Gasielis (Miere Matien)	
the bottom of the front panel) Ethernet (NTWK1, NTWK2)	Communication Standard Signals Supplied Baud Rate Format Speed Media Connectivity Protocol	RS232D Tx, Rx, CTS, GND 2400, 4800, 9600, 19200, 38400, 57600 Config600 Protocol 10 or 100 Mb/s, full Duplex 10 or 100baseT, twisted pair utilizing standard RJ45 Modbus/TCP or Modbus over Ethernet Master, slave, and peer-to-peer Support for gas chromatographs, ultrasonic (Daniel, Instromet, Caldon, and Sick), and Coriolis (Micro Motion)	
the bottom of the front panel) Ethernet (NTWK1, NTWK2)	Communication Standard Signals Supplied Baud Rate Format Speed Media Connectivity Protocol	RS232D Tx, Rx, CTS, GND 2400, 4800, 9600, 19200, 38400, 57600 Config600 Protocol 10 or 100 Mb/s, full Duplex 10 or 100baseT, twisted pair utilizing standard RJ45 Modbus/TCP or Modbus over Ethernet Master, slave, and peer-to-peer Support for gas chromatographs, ultrasonic (Daniel, Instromet, Caldon, and Sick), and Coriolis (Micro Motion) Can support multiple printers for separate reports, alarms, and events	
the bottom of the front panel) Ethernet (NTWK1, NTWK2)	Communication Standard Signals Supplied Baud Rate Format Speed Media Connectivity Protocol Network printers Connector	RS232D Tx, Rx, CTS, GND 2400, 4800, 9600, 19200, 38400, 57600 Config600 Protocol 10 or 100 Mb/s, full Duplex 10 or 100baseT, twisted pair utilizing standard RJ45 Modbus/TCP or Modbus over Ethernet Master, slave, and peer-to-peer Support for gas chromatographs, ultrasonic (Daniel, Instromet, Caldon, and Sick), and Coriolis (Micro Motion) Can support multiple printers for separate reports, alarms, and events FCC-68 RJ45	
the bottom of the front panel) Ethernet (NTWK1, NTWK2) RS232 (COM3, COM4)	Communication Standard Signals Supplied Baud Rate Format Speed Media Connectivity Protocol Network printers Connector Communication Standard	RS232D Tx, Rx, CTS, GND 2400, 4800, 9600, 19200, 38400, 57600 Config600 Protocol 10 or 100 Mb/s, full Duplex 10 or 100baseT, twisted pair utilizing standard RJ45 Modbus/TCP or Modbus over Ethernet Master, slave, and peer-to-peer Support for gas chromatographs, ultrasonic (Daniel, Instromet, Caldon, and Sick), and Coriolis (Micro Motion) Can support multiple printers for separate reports, alarms, and events FCC-68 RJ45 RS232D	
the bottom of the front panel) Ethernet (NTWK1, NTWK2) RS232 (COM3, COM4)	Communication Standard Signals Supplied Baud Rate Format Speed Media Connectivity Protocol Network printers Connector Communication Standard Signals Supplied	RS232D Tx, Rx, CTS, GND 2400, 4800, 9600, 19200, 38400, 57600 Config600 Protocol 10 or 100 Mb/s, full Duplex 10 or 100baseT, twisted pair utilizing standard RJ45 Modbus/TCP or Modbus over Ethernet Master, slave, and peer-to-peer Support for gas chromatographs, ultrasonic (Daniel, Instromet, Caldon, and Sick), and Coriolis (Micro Motion) Can support multiple printers for separate reports, alarms, and events FCC-68 RJ45 RS232D Tx, Rx, RTS, CTS, DTR, DSR, GND, DCD	
the bottom of the front panel) Ethernet (NTWK1, NTWK2) RS232 (COM3, COM4)	Communication Standard Signals Supplied Baud Rate Format Speed Media Connectivity Protocol Network printers Connector Communication Standard Signals Supplied Baud Rate	RS232D Tx, Rx, CTS, GND 2400, 4800, 9600, 19200, 38400, 57600 Config600 Protocol 10 or 100 Mb/s, full Duplex 10 or 100baseT, twisted pair utilizing standard RJ45 Modbus/TCP or Modbus over Ethernet Master, slave, and peer-to-peer Support for gas chromatographs, ultrasonic (Daniel, Instromet, Caldon, and Sick), and Coriolis (Micro Motion) Can support multiple printers for separate reports, alarms, and events FCC-68 RJ45 RS232D Tx, Rx, RTS, CTS, DTR, DSR, GND, DCD 2400, 4800, 9600, 19200, 38400, 57600	

	Data Protocol	ASCII, MODBUS (ASCII, RTU) Master, slave, and peer-to-peer		
		Support for printer Instromet, Caldon	rs, gas chromatographs, ultrasonic (Daniel, , and Sick), and Coriolis (Micro Motion)	
RS422/RS485	Connector	Standard screw ter	rminals, 3.5 mm pitch	
(COM5, COM6, COM7)	Communication	Point-to-point	RS422	
	Standard	Multi-drop	RS422 or RS485	
	Signals Supplied	Tx+, Tx-, Rx+, Rx-,	common shield	
	Termination Resistor	Jumper-selectable		
	Baud Rate	2400, 4800, 9600, 19200, 38400, 57600		
	Format	Software controlled on each channel		
	Data Protocol	ASCII, MODBUS (ASCII, RTU)		
RS485	Connector	Standard screw ter	rminals, 3.5 mm pitch	
(COM9, COM10, COM11, COM12)	Communication Standard	Multi-master	2-wire RS485	
	Signals Supplied	Tx, Rx, common sh	nield	
	Baud Rate	2400, 4800, 9600,	, 19200, 38400, 57600	
	Format	Software controlled on each channel		
	Data Protocol	ASCII, MODBUS (ASCII, RTU)		
USB	Connector	USB-A		
	Protocol	USB 2.0		
		Extract reports to l	USB flash drive (VFAT32 format)	
Inputs and Outputs				
Analog Inputs	Туре	1 to 5 V, 0 to 5 V, 4 of 5 single-ended v common return; c	1 to 5 V, 0 to 5 V, 4 to 20 mA, or 0 to 20 mA, opto-isolated. Two groups of 5 single-ended voltage or current inputs with each group sharing a common return; channels 11 and 12 are current input only.	
	Signal Level	0 to 5 V or 0 to 22 mA		
	Scan Rate	All channels can be acquired in less than 1 second		
	Resolution	24 bits, auto-zero, auto-calibrate		
	Conversion Time	Less than 100 ms per channel		
	Series Mode Rejection	>100 dB at 50 Hz and 60 Hz		
	Voltage Common Mode Range	±50 V as a group relative to computer ground		
	Common Mode Rejection	>100 dB at 50 Hz and 60 Hz		
	Input Impedance	>10 M $\Omega$ (voltage mode), approx 250 $\Omega$ (current mode)		
	Calibration Period	2 years to 0.005% of voltage 5 years to 0.01% of voltage		
	A/D Converter Inputs - Voltage Mode	Type of Inputs	Single-ended voltage inputs	
		Input Range	0 to 5 V	
		Accuracy	±0.005% of FSD at 23°C (73°F)	
		Ambient Temperature Effect	± 7 ppm/°C (± 4 ppm/°F) from 23°C (73°F) in the range 0 to 45°C (32 to 113°F)	

	A/D Converter Inputs - Current Mode	Type of Inputs	Single-ended current inputs	
		Input Range	0 to 22 mA	
	Mode	Accuracy	± 0.02% of FSD at 23°C (73°F)	
		Ambient Temperature Effect	± 10 ppm/°C (± 5.5 ppm/°F) from 23 °C in the range 0 to 45 °C (32 to 113 °F)	
Frequency/Density Inputs	Туре	dc coupled, opto-i	solated	
	Signal Level	3 V min pk-pk		
	Maximum Input Voltage	12 V pk-pk		
	Current Limit	Internally limited to 3 mA		
	Frequency Range	0 to 10 kHz		
	Accuracy	20 ppm		
	Resolution	5 nanoseconds		
Pulse Inputs – Flow	Туре	Dual pulse or singl	e pulse train, opto-isolated	
	Signal Level	±3.5 V to ±24 V, m	inimum 5 mA	
	Frequency Range	1Hz to 10 kHz		
	Security Monitoring	IP 252/76 (ISO 655	51), level A or B	
Digital Status Inputs	Туре	16 opto-isolated ir positive connectio	nputs, arranged in 4 groups of 4 with common n to allow simple interface to open collector outputs	
	Max Input Voltage	30 V		
	Min Input On Voltage	12 V		
	Max Input Off Voltage	3 V		
	Input Impedance	2 to 2.5 k $\Omega$ typical		
	Protection	Reverse voltage protection		
PRT (RTD) Inputs	Туре	4-wire only connec	ction using Pt 100 transducers, opto-isolated	
	PRT (RTD) Resistance	100 Ω [Pt 100 to IE (American 0.0039)	EC 751/DIN 43760 (Europe 0.00385), IPTS68 2), Callendar-Van Dusen]	
	<b>Excitation Current</b>	1 mA nominal		
	Measuring Range	60 to 216 Ω (–100	°C to +300°C) (–148°F to +572°F)	
	Resolution	0.01°C (0.018°F)		
	Accuracy	–100°C to 200°C (- 200°C to 300°C (39	–148°F to 392°F) ± 0.01% 92°F to 572°F) ± 0.02%	
	PRT (RTD) Cables	Core resistance up to $600 \Omega$		
	Barriers	9 V, 100 $\Omega$ are satisfactory		
	Security	Continuous cable/PRT (RTD) integrity tests for earths/ground faults and open circuits		
Analog Outputs	Туре	4 to 20 mA outputs, opto-isolated		
	Resolution	12-bit minimum		
	Accuracy	± 0.1% at 23°C (73°F)		
	Ambient Temperature Effect	20 ppm/°C (11ppn	n/°F) from 23°C (73°F)	
	Load Loop Resistance	$650 \Omega$ maximum when powered by 15 V local isolated source 470 Ω – 1000 Ω when powered from 24 V external supply		

	Maximum External Supply	32 V	
	Output Form	Controlled active current sink to ground return of local floating supply	
	Number of Field Connections	3 terminals per channel	
	Update Time	Less than one second	
Digital Outputs	Туре	3 groups of 4 with common negative, opto-isolated	
	Frequency Range	0 to 0.5 Hz	
	Max Output Saturation Voltage	1.5 V @ 100 mA	
	Low current Saturation Voltage	600 mV @ 1 mA to suit TTL style input, with 4.7 $k\Omega$ pull-up to 5 V	
	Max Output Standoff Voltage	42 V (limited by transorb)	
	Max Output Current	100 mA	
	Reset/Power on State	All digital outputs OFF	
Pulse Outputs	Туре	Opto-isolated open-collectors	
	Frequency Range	0 to 100 Hz	
	Max Output Current	100 mA	
	Max Output Saturation Voltage	1.5 V @ 100 mA	
	Low Current Saturation Voltage	600 mV @ 1 mA to suit TTL style input	
	Max Output Standoff Voltage	42 V (limited by transorb)	
Raw Pulse Outputs	Туре	Digital ground-referenced open-collector	
	Gating	Software controlled	
	Max Output Saturation	1.5 V	
	Max Output Standoff Voltage	26 V (limited by transorb)	
	Max Output Current	100 mA	
	Frequency Range	0 to 10 kHz	
	Minimum On Period	100 μs (microseconds)	
	Use	To bus together several streams to a common prover computer	

## **Expansion Modules**

The FloBoss S600+ is supplied with one I/O (P144) module and one Pulse Mezzanine (P148) module as standard. Two additional module slots are available. Optional modules include the following:

I/O (P144) Module	Provides the S600+ with additional analog and digital I/O		
(1 standard, additional modules are optional)	Analog Inputs	Quantity	12
	Analog Outputs	Quantity	4
	Digital Inputs	Quantity	16
	Digital Outputs	Quantity	12

	Pulse Inputs – Flow (requires Pulse Mezzanine module)	Quantity	2 dual pulse or 4 single pulse	
	Frequency Density Inputs	Quantity	3	
	PRT (RTD) Inputs	Quantity	3	
	Pulse Outputs	Quantity	5	
	Raw Pulse Output	Quantity	1, raw pulse output for proving, 0 to 10 kHz	
Pulse Mezzanine (P148)	Provides S600+ with pulse input capability.			
Module	Quantity	2 dual pulse or 4 <b>Note:</b> The Pul on an I/ additio	4 single pulse Ise Mezzanine module is installed as a daughter board /O (P144) or Prover (P154) module and does not use an nal module slot.	
Prover (P154) Module	ule Provides the S600+ with an interface to a prover		o a prover	
(optional)	Prover Types	Compact, uni-d chronometry. U	irectional, bi-directional, master meter, dual Jp to 4 sphere switch	
	Digital Inputs	Quantity	32	
	Digital Outputs	Quantity	12	
	Pulse Inputs – Flow (requires Pulse Mezzanine module)	Quantity	2 dual pulse or 4 single pulse	
	Frequency Density Inputs	Quantity	2	
	Pulse Outputs	Quantity	4	
	Raw Pulse Input	Quantity	3	
	Phase Loop Lock Input	Quantity	1	
	Switch Detect	Quantity	4	
HART (P188) Module	Provides the S600+ w	ith an interface to	o HART transmitters	
(optional)	Quantity	12 channels. Ea drop communic up to 8 transmit	ch channel can be configured for point-point or multi- cations. In multi-drop mode, each channel can support tters.	
	Modes	Supports dual n used to change burst mode.	naster (primary or secondary), read only (cannot be constants on the HART device). Does not support	
	Max. Number of HART Transmitters	50		
Power				
Supply Voltage	20 to 32 Vdc, 30 Vdc	nominal, 48 W m	aximum	
	Typical	18 W with 1 I/O	module	
		24 W with 2 I/O	modules	
		36 W with 3 I/O	modules	
Protection	2.5 A anti-surge slow	blow fuse		
Inrush Current	Thermistor protectio	n providing 6 A at	25°C	
Supply Isolation	Three-way, galvanically isolated from input to computer, supply and ground, 50 V			
Hold-up Period	> 10 ms after power f	ail flag		
Maximum Input Ripple	2 V pk-pk			

Input Power Fail Flag	17 to19 Vdc	
Power Outputs	24 Vdc, 500 mA	
	15 Vdc, 100 mA	
	50 Vdc isolation	
	The outputs are isola	ited from the supply voltage and from the computer.
Physical		
Enclosure	Туре	Painted, welded steel outer case with plastic front panel
	Classification	IP50 from front panel
Dimensions	Case	84.5 mm W by 270 mm H by 303.8 mm D (3.327 in. W by 10.63 in. H by 11.94 in. D)
	Display Keypad Molding	85 mm W by 269 mm H by 28 mm D (3.35 in. W by 10.59 in. H by 1.10 in. D)
	Panel Cutout	66 mm W by 150 mm H (2.6 in. W by 5.9 in. H) with ±1 mm tolerance
	Pitch Between Cases	110 mm (4.33 in.) giving 25 mm (0.98 in.) air gap
	Max Panel Thickness	10 mm (0.39 in.)
Weight	4.3 kg (9.48 lb) appr	oximate with a single I/O module configuration
Circuit Boards	Eurocard-compatible	e, slide in and out from the rear
Access	Allow 300 mm (11.8	1 in.) clearance directly behind case for maintenance
Display-Keypad	Graphics Display	LCD 128 x 64 pixel (8 lines of 20 alpha-characters) with LED backlight, using a Toshiba T6963 LCD controller
	Keyboard	29 self-colored silicon rubber keys with tactile feel
	Alarm/Status	3 color LED (green, amber, red)
	Configuration Port	RJ12 connector for the Config600 package on the bottom of the front panel molding
	Languages	The display supports English and Russian character sets
Environmental		
Operating Temperature	−10 °C to 55 °C (14 °F to 131 °F)	
Storage Temperature		
Relative Humidity	90% non-condensing	
Conformal Coating	All circuit boards are conformal coated.	
Safety Classification	For use in a classified safe electrical area	
Approvals		
Approval Standards	CE	EMC Directive 2014/30/EU
EMC Standards	IEC 61000-4-2 (Electrostatic Discharge) IEC 61000-4-3 (Radiated Immunity) IEC 61000-4-4 (Fast Transients) IEC 61000-4-5 (Surges) IEC 61000-4-6 (Conducted RF) IEC 61000-4-8 (Power Frequency Magnetic Field) IEC 61000-4-29 (Voltage Dips, Interrupts & Tolerance) IEC 55022 (Radiated Emissions)	
Metrology Standards	<u>N</u> Mİ	MID M1/E2 (Gas) of European Directive 2014/32/EU in accordance with WELMEC 8.8 EN 12405-1:2005+A2:2010 MID M1/E2 (Liquid) of European Directive 2014/32/EU in accordance with WELMEC 8.8 OIML R117-1. Ed 2007

		INMETRO, Portaria Inmetro/Dimel n.º 188, de 30 de setembro de 2016
	INMETRO	
	ONML	ONML (L'Office National de Métrologie Légale), Algeria Cert 518/DIR/ONML/DT/MF/DW/12
Miscellaneous Approvals	Customs Union	EAC
		TR CU 004/2011, TR CU 020/2011 Certified by "Technoneftegaz" TC RU C-US.HO03.B.00304 valid from 30.06.2015 to 29.06.2020
	RoHS2	RoHS2 EU Directive 2011/65/EU
	RoHS (China)	25

For customer service and technical support, visit <u>www.Emerson.com/SupportNet</u>

## Global Headquarters,

North America, and Latin America: Emerson Automation Solutions Remote Automation Solutions 6005 Rogerdale Road Houston, TX 77072 U.S.A. T +1 281 879 2699 | F +1 281 988 4445 www.Emerson.com/RemoteAutomation

#### Europe:

Emerson Automation Solutions Remote Automation Solutions Unit 1, Waterfront Business Park Dudley Road, Brierley Hill Dudley DY5 1LX UK T +44 1384 487200 | F +44 1384 487258

## Middle East/Africa:

Emerson Automation Solutions Remote Automation Solutions Emerson FZE P.O. Box 17033 Jebel Ali Free Zone – South 2 Dubai U.A.E. T +971 4 8118100 | F +971 4 8865465

### Asia-Pacific:

Emerson Automation Solutions Remote Automation Solutions 1 Pandan Crescent Singapore 128461 T +65 6777 8211 | F +65 6777 0947 © 2012–2019 Remote Automation Solutions, a business unit of Emerson Automation Solutions. All rights reserved.

This publication is for informational purposes only. While every effort has been made to ensure accuracy, this publication shall not be read to include any warranty or guarantee, express or implied, including as regards the products or services described or their use or applicability. Remote Automation Solutions (RAS) reserves the right to modify or improve the designs or specifications of its products at any time without notice. All sales are governed by RAS terms and conditions which are available upon request. RAS accepts no responsibility for proper selection, use or maintenance of any product, which remains solely with the purchaser and/or end-user.

